


### UNDERCOUNTER KITCHEN SINK K-3351 ALSO K-3351-L

#### Features

- 18-gauge stainless steel
- Double (equal) compartment
- Undercounter
- Includes installation hardware
- Squared bowl(s)
- 29-1/4" (74.3 cm) x 15-3/4" (40 cm)
- 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin (K-3351)
- 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin (K-3351-L)



#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

#### Colors/Finishes

- NA: None applicable

#### Accessories:

- CP: Polished Chrome
- 0: White
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

#### Specified Model

Model	Description	Colors/Finishes
K-3351	Undercounter sink with 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin	<input type="checkbox"/> NA
K-3351-L	Undercounter sink with 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin	<input type="checkbox"/> NA

Optional Accessories			
K-3190	Bottom basin rack (for either basin)	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other _____
K-3277	Wire basket (for either basin)	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other _____
K-3294	Hardwood cutting board (for either basin)	<input type="checkbox"/> NA	
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____

#### Product Specification:

The undercounter sink shall be 29-1/4" (74.3 cm) in length and 15-3/4" (40 cm) in width. Sink shall be made of 18 gauge stainless steel. Sink shall be double (equal) compartment with squared bowls. Kohler Model K-3351 sink shall have 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin. Kohler Model K-3351-L sink shall have 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm). Sink shall include installation hardware. Sink shall be Kohler Model K-3351-\_\_\_\_\_.

# UNDERTONE®


## Technical Information

Dimensions shown for K-3351; sink dimensions are opposite for K-3351-L.		
Fixture:*	basin area	water depth
Sink, left	14" (35.6 cm) x 16" (40.6 cm)	9-1/2" (24.1 cm)
Sink, right	14" (35.6 cm) x 16" (40.6 cm)	7-1/2" (19.1 cm)
Drain Holes	3-5/8" (9.2 cm) D.	
* Approximate measurements for comparison only.		

Included Components:	
Hardware kit (4 required)	91915
Cutout template	1040556-7

## Installation Notes

Install this product according to the installation guide.



## Product Diagram